



□□□□□

Eaton FRD232P

Eaton Crouse-Hinds series Pauluhn Meridian FRD marine interior, 50/60 Hz, 4 ft, Acrylic lens, T8, Galvanized steel, Recessed ceiling mount, 2-lamp, Parabolic louver, 120-277 Vac, 32W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Pauluhn Meridian FRD marine interior
CATALOG NUMBER	FRD232P
UPC	662276397088
PRODUCT LENGTH/DEPTH	50.63 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	10.81 in
PRODUCT WEIGHT	23 lb

Certifications and compliances	
AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications	
LAMP LENGTH	4 ft
LIGHT TYPE	T8
NUMBER OF LAMPS	2-lamp
WATTAGE	32W
VOLTAGE RATING	120-277 Vac
FREQUENCY RATING	50/60 Hz
MOUNTING METHOD	Recessed ceiling
MATERIAL	Galvanized steel
LENS MATERIAL	Acrylic
SPECIAL FEATURES	Parabolic louver

Links	
IF LBL1342 - FRD	IF LBL1342 - FRD Fluorescent Luminaires
Eaton Specification Sheet - FRD232P	Eaton Specification Sheet - FRD232P
Crouse-Hinds series FRD Marine Interior Continuous Plank Recessed Lights catalog page	Crouse-Hinds series FRD Marine Interior Continuous Plank Recessed Lights catalog page
