



Eaton FT3CC4IWLS18IP

Eaton FlexiTech, Combined Ceiling, 30m, 4
picto. (DRLU), WLS, 1 to 8H, IP65

□□□□

PRODUCT NAME	Eaton FlexiTech CC SC emergency luminaire
CATALOG NUMBER	FT3CC4IWLS18IP
PRODUCT LENGTH/DEPTH	325 mm
PRODUCT HEIGHT	208 mm
PRODUCT WIDTH	51 mm
PRODUCT WEIGHT	0.001 kg
CERTIFICATIONS	CE

BATTERY QUALITY	Lithium-ion
PROTECTION CLASS	II
DEGREE OF PROTECTION	IP65
LAMP TYPE	LED not exchangeable
WITH LIGHT SOURCE	Yes
LAMP HOLDER	None
TYPE OF INDICATOR	Single/double-sided
MONITORING EQUIPMENT	Safety module for monitoring (central feeded system)
POWER SUPPLY SYSTEM	Peripheral (individual battery)
VOLTAGE TYPE	AC
POWER FACTOR	0.49
WITH REMOTE SWITCH CONNECTION	No
ENERGY EFFICIENCY CLASS	A
CONDUCTOR CROSS SECTION	2.5
CONNECTION TYPE	Plug-in connection
MAX. SYSTEM POWER	3.9 W
TYPE OF CONTROL GEAR	LED operating device current-controlled
TYPE OF WIRING	Suitable for through wiring
NOMINAL VOLTAGE AC - MAX	230 V
NOMINAL VOLTAGE AC - MIN	230 V
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN	5 °C
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX	45 °C
NOMINAL OPERATION TIME - MIN	8 hour
NOMINAL OPERATION TIME - MAX	1 hour
SUITABLE FOR STANDBY SWITCHING	No
SUITABLE FOR CONTINUOUS CIRCUIT	No
RAL-NUMBER (SIMILAR) HOUSING	9003
MOUNTING METHOD	Ceiling surface mounting
MATERIAL HOUSING	Plastic
COLOR HOUSING	White

MATERIAL COVER	Plastic, transparent
LABELLING TYPE	Insert sheet/plate
PICTOGRAM INCLUDED	Yes
NUMBER OF POLES (NUMERIC)	3
IMPACT STRENGTH	IK07
RATED LUMINOUS FLUX ACC. IEC 62722-2-1	240 lm
COLOR TEMPERATURE - MAX	6500 K
COLOR TEMPERATURE - MIN	6500 K
LIGHT DISTRIBUTOR	Diffuser lens/optic/panel
FUNCTION	Escape route lighting/signage
LUMINAIRE WITH LIMITED SURFACE TEMPERATURE, SIGN D	No
NUMBER OF LIGHTING HEADS	1
VIEWING DISTANCE	30 m
PRODUCT BRANDING	Eaton
WITH REMOTE CONTROL	No
CONSTANT LIGHT OUTPUT (CLO)	No
EXCHANGEABLE CONTROL GEAR	No

□□□□:
□□□□:
□□□:
□□: