



## Eaton FT3CW4IWLS18IP

Eaton FlexiTech, Combined Wall, 30m, 4  
picto. (DRLU), WLS, 1 to 8H, IP66

□□□□

|                                 |                                              |
|---------------------------------|----------------------------------------------|
| <b>PRODUCT NAME</b>             | Eaton FlexiTech CW SC<br>emergency luminaire |
| <b>CATALOG NUMBER</b>           | FT3CW4IWLS18IP                               |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 326 mm                                       |
| <b>PRODUCT HEIGHT</b>           | 192 mm                                       |
| <b>PRODUCT WIDTH</b>            | 38 mm                                        |
| <b>PRODUCT WEIGHT</b>           | 1 kg                                         |
| <b>CERTIFICATIONS</b>           | CE                                           |

|                                            |                                                      |
|--------------------------------------------|------------------------------------------------------|
| BATTERY QUALITY                            | Lithium-ion                                          |
| PROTECTION CLASS                           | II                                                   |
| DEGREE OF PROTECTION                       | IP66<br>IP65                                         |
| LAMP TYPE                                  | LED not exchangeable                                 |
| WITH LIGHT SOURCE                          | Yes                                                  |
| LAMP HOLDER                                | None                                                 |
| TYPE OF INDICATOR                          | Only single-sided                                    |
| MONITORING EQUIPMENT                       | Safety module for monitoring (central feeded system) |
| POWER SUPPLY SYSTEM                        | Peripheral (individual battery)                      |
| VOLTAGE TYPE                               | AC                                                   |
| POWER FACTOR                               | 0.45                                                 |
| WITH REMOTE SWITCH CONNECTION              | No                                                   |
| ENERGY EFFICIENCY CLASS                    | A                                                    |
| CONDUCTOR CROSS SECTION                    | 2.5                                                  |
| CONNECTION TYPE                            | Plug-in connection                                   |
| MAX. SYSTEM POWER                          | 2.5 W                                                |
| TYPE OF CONTROL GEAR                       | LED operating device current-controlled              |
| TYPE OF WIRING                             | Suitable for through wiring                          |
| NOMINAL VOLTAGE AC - MAX                   | 230 V                                                |
| NOMINAL VOLTAGE AC - MIN                   | 230 V                                                |
| RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN | 5 °C                                                 |
| RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX | 45 °C                                                |
| NOMINAL OPERATION TIME - MIN               | 8 hour                                               |
| NOMINAL OPERATION TIME - MAX               | 1 hour                                               |
| SUITABLE FOR STANDBY SWITCHING             | No                                                   |
| SUITABLE FOR CONTINUOUS CIRCUIT            | No                                                   |
| RAL-NUMBER (SIMILAR) HOUSING               | 9003                                                 |
| MOUNTING METHOD                            | Wall surface mounted                                 |
| MATERIAL HOUSING                           | Plastic                                              |

|                                                    |                               |
|----------------------------------------------------|-------------------------------|
| COLOR HOUSING                                      | White                         |
| MATERIAL COVER                                     | Plastic, transparent          |
| LABELLING TYPE                                     | Insert sheet/plate            |
| PICTOGRAM INCLUDED                                 | Yes                           |
| NUMBER OF POLES (NUMERIC)                          | 3                             |
| IMPACT STRENGTH                                    | IK07                          |
| RATED LUMINOUS FLUX ACC. IEC 62722-2-1             | 240 lm                        |
| COLOR TEMPERATURE - MAX                            | 6500 K                        |
| COLOR TEMPERATURE - MIN                            | 6500 K                        |
| LIGHT DISTRIBUTOR                                  | Diffuser lens/optic/panel     |
| FUNCTION                                           | Escape route lighting/signage |
| LUMINAIRE WITH LIMITED SURFACE TEMPERATURE, SIGN D | No                            |
| NUMBER OF LIGHTING HEADS                           | 1                             |
| VIEWING DISTANCE                                   | 30 m                          |
| PRODUCT BRANDING                                   | Eaton                         |
| WITH REMOTE CONTROL                                | No                            |
| CONSTANT LIGHT OUTPUT (CLO)                        | No                            |
| EXCHANGEABLE CONTROL GEAR                          | No                            |

|       |
|-------|
| □□□□: |
| □□□□: |
| □□□:  |
| □□:   |