



□□□□□

## Eaton FWA-225B

Eaton Bussmann series FWA high speed fuse, 500 Vac (0.25-6.3A), 500 Vdc (2-5A), 225A, None, High speed fuse

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed cylindrical fuse
<b>CATALOG NUMBER</b>	FWA-225B
<b>UPC</b>	051712577984
<b>PRODUCT LENGTH/DEPTH</b>	25.4 mm
<b>PRODUCT HEIGHT</b>	25.4 mm
<b>PRODUCT WIDTH</b>	67 mm
<b>PRODUCT WEIGHT</b>	83 g
<b>COMPLIANCES</b>	Contact factory Contact Manufacturer

AMPERAGE RATING	225 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Non Indicating
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	100 A
RATED VOLTAGE AC	150 V
RATED VOLTAGE DC	150 V
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	50 mm
CURRENT TYPE	AC/DC
CLASS	Class aR
CLEARING (I <sub>2</sub> T)	45000
WATT LOSSES	17.6 W
FUSE SHAPE	Cylindrical, center bolted tags
PRE ARC (I <sub>2</sub> T)	4780
COLOR	None
INTERRUPT RATING	100 kAIC at 150 Vac 100 kAIC at 80 Vdc 20 kAIC at 150 Vdc
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	150 Vac/dc
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

