

## Eaton FWH-200B

Eaton Bussmann series FWH high speed fuse, 500 Vac/dc (UL), 200A, 200 kAIC at 300 Vdc, 50 kAIC at 300 Vdc, None, High speed fuse, Blade end X blade end, Class aR, Stud, White, Ceramic

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed cylindrical fuse
<b>CATALOG NUMBER</b>	FWH-200B
<b>UPC</b>	051712795869
<b>PRODUCT LENGTH/DEPTH</b>	91 mm
<b>PRODUCT HEIGHT</b>	30 mm
<b>PRODUCT WIDTH</b>	30 mm
<b>PRODUCT WEIGHT</b>	152 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	UL Recognized CSA Certified

AMPERAGE RATING	200 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Non Indicating
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	500 V
RATED VOLTAGE DC	500 V
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	74.09 mm
CURRENT TYPE	AC/DC
CLASS	Class aR
CLEARING (I2T)	8500
WATT LOSSES	40 W
FUSE SHAPE	Center bolted tags
PRE ARC (I2T)	1900
COLOR	White
INTERRUPT RATING	200 kAIC at 300 Vdc 50 kAIC at 300 Vdc
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MATERIAL	Ceramic
MOUNTING METHOD	Stud
QUANTITY	1
VOLTAGE RATING	500 Vac, 500 Vdc
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWH-B
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

