

## Eaton FWH-3A14F

Eaton Bussmann series FWH high speed fuse, 750 Vac, 750 Vdc, 3A, 200 kAIC Vac, 50 kAIC at 500 Vdc, Non Indicating, High speed fuse, Ferrule end X ferrule end

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWH-3A14F
UPC	051712795074
PRODUCT LENGTH/DEPTH	14 mm
PRODUCT HEIGHT	14 mm
PRODUCT WIDTH	51 mm
PRODUCT WEIGHT	20.4 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	CSA Certified UL Recognized

AMPERAGE RATING	3 A
ACCESSORIES	<ul style="list-style-type: none"> <li>• CH14 Modular fuse holder</li> <li>• FW14-PCB</li> </ul>
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Other
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	14 x 51 mm
RATED VOLTAGE AC	500 V
CLASS	Class aR
WATT LOSSES	2.3 W
FUSE SHAPE	Cylindrical
INTERRUPT RATING	50 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	14 mm x 51 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	500 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWH-A14F
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	50 kA



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

