



## Eaton FWH-50B

Eaton Bussmann series FWH high speed fuse, 1200V, 50A, 200 kAIC at 1000 Vac, 50 kAIC at 500 Vdc, None, High speed fuse, Blade end X blade end, Stud

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed cylindrical fuse
<b>CATALOG NUMBER</b>	FWH-50B
<b>UPC</b>	051712795777
<b>PRODUCT LENGTH/DEPTH</b>	108 mm
<b>PRODUCT HEIGHT</b>	28 mm
<b>PRODUCT WIDTH</b>	90 mm
<b>PRODUCT WEIGHT</b>	63 g
<b>COMPLIANCES</b>	CE Marked
<b>CERTIFICATIONS</b>	UL Recognized CSA Certified

□□□□

□□

AMPERAGE RATING	50 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Non Indicating
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	500 V
RATED VOLTAGE DC	500 V
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	60.75 mm
CURRENT TYPE	AC/DC
CLASS	Class aR
CLEARING (I2T)	670
WATT LOSSES	7.5 W
FUSE SHAPE	Cylindrical, center bolted tags
PRE ARC (I2T)	135
COLOR	None
INTERRUPT RATING	200 kAIC at 1000 Vac 50 kAIC at 500 Vdc
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Stud
VOLTAGE RATING	500 Vac, 500 Vdc
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWH-B
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

