



Eaton FWH-60B

Eaton Bussmann series FWH high speed fuse, 1000 Vdc, 60A, 200 kAIC at 1000 Vac, 50 kAIC at 500 Vdc, None, High speed fuse, Blade end X blade end, Stud

□□□□

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWH-60B
UPC	051712795784
PRODUCT LENGTH/DEPTH	108 mm
PRODUCT HEIGHT	28 mm
PRODUCT WIDTH	90 mm
PRODUCT WEIGHT	63 g
COMPLIANCES	CE Marked
CERTIFICATIONS	CSA Certified UL Recognized

AMPERAGE RATING	60 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Non Indicating
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	500 V
RATED VOLTAGE DC	500 V
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	60.75 mm
CURRENT TYPE	AC/DC
CLASS	Class aR
CLEARING (I2T)	900
WATT LOSSES	9.9 W
FUSE SHAPE	Cylindrical, center bolted tags
PRE ARC (I2T)	210
COLOR	None
INTERRUPT RATING	50 kAIC at 500 Vdc 200 kAIC at 1000 Vac
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Stud
VOLTAGE RATING	500 Vac, 500 Vdc
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWH-B
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

