

Eaton FWJ-30A14F

Eaton Bussmann series FWJ high speed fuse, 700 Vac/dc, 30A, 20 kAIC Vac/dc, Non Indicating, High speed fuse, Ferrule end X ferrule end

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWJ-30A14F
UPC	051712796125
PRODUCT LENGTH/DEPTH	60 mm
PRODUCT HEIGHT	40 mm
PRODUCT WIDTH	86 mm
PRODUCT WEIGHT	27.6 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized

AMPERAGE RATING	30 A
ACCESSORIES	• CH14 Modular fuse holder • FW14-PCB
BREAKING CAPACITY	25 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Non Indicating
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	14 x 51 mm
RATED VOLTAGE AC	1000 V
RATED VOLTAGE DC	800 V
CLASS	Class aR
CLEARING (I2T)	450
WATT LOSSES	14 W
FUSE SHAPE	Cylindrical
PRE ARC (I2T)	52
INTERRUPT RATING	25 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	14 mm x 51 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	500 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWJ-A14F
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	25 kA
BREAKING CAPACITY AT NOMINAL VOLTAGE, DC	50 kA

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

