



Eaton FWL-30A20FI

Eaton Bussmann series high speed traction fuse, 700 Vac/dc, 30A, 50 kAIC, With Indicator, Fuse, Class gS

□□□□

PRODUCT NAME	Eaton Bussmann series high speed traction fuse
CATALOG NUMBER	FWL-30A20FI
UPC	051712640367
PRODUCT LENGTH/DEPTH	127 mm
PRODUCT HEIGHT	20 mm
PRODUCT WIDTH	20 mm
PRODUCT WEIGHT	104.7 g
COMPLIANCES	CE Marked
CERTIFICATIONS	IEC Rated



Powering Business Worldwide



AMPERAGE RATING	30 A
BREAKING CAPACITY	50 kA
WITH STRIKER	Yes
VOLTAGE TYPE	AC/DC
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
RELEASE CHARACTERISTIC	Other
FUSE INDICATOR	With Indicator
FREQUENCY RATING - MIN	45 Hz
FREQUENCY RATING - MAX	62 Hz
FUSE SIZE	20 x 127 mm
CLASS	Class gG
CLEARING (I2T)	4300 at 750 Vdc
WATT LOSSES	7.5 W
FUSE SHAPE	Cylindrical
PRE ARC (I2T)	1850
MOUNTING DIMENSION	Other
CURRENT TYPE	DC
RATED VOLTAGE AC	1200 V
RATED VOLTAGE DC	1000 V
COLOR	None
INTERRUPT RATING	50 kA at 1000 Vdc
CONSTRUCTION SIZE	Other
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	1200 V
FUSE TYPE	FWL-A20FI
TYPE	Fuse
APPLICATION	traction
SUITABLE FOR	CH127 Fuse holder
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	50 kA
BREAKING CAPACITY AT NOMINAL VOLTAGE, DC	50 kA



DECLARATIONS OF CONFORMITY

[eaton-high-speed-traction-fuse-declaration-of-conformity-uk250962en.pdf](#)

