



□□□□□

Eaton FWP-1A14F

Eaton Bussmann series FWP high speed fuse, 700V (UL), 1A, 200 kAIC, Non Indicating, High speed fuse, Ferrule end X ferrule end, Class aR, White, Ceramic

□□□□

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWP-1A14F
UPC	051712795098
PRODUCT LENGTH/DEPTH	51 mm
PRODUCT HEIGHT	15 mm
PRODUCT WIDTH	15 mm
PRODUCT WEIGHT	20.6 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	CSA Certified UL Recognized



Powering Business Worldwide

□□□□

AMPERAGE RATING 1 A

ACCESSORIES

- CH14 Modular fuse holder
- FW14-PCB

BREAKING CAPACITY 200 kA

FREQUENCY RATING - MAX 62 Hz

FREQUENCY RATING - MIN 45 Hz

FUSE INDICATOR Non Indicating

RELEASE CHARACTERISTIC Other

UTILIZATION CATEGORY aR (accompanied semiconductor protection)

VOLTAGE TYPE AC/DC

FUSE SIZE 14 x 51 mm

RATED VOLTAGE AC 700 V

CLASS Class aR

CLEARING (I₂T) 0.41

WATT LOSSES 5.7 W

FUSE SHAPE Cylindrical

PRE ARC (I₂T) 0.04

COLOR White

INTERRUPT RATING 200 kAIC

CONNECTION Ferrule end x ferrule end

CONSTRUCTION SIZE 14 mm x 51 mm

MATERIAL Ceramic

PACKAGING TYPE Standard

VOLTAGE RATING 700 V

TYPE High speed fuse

APPLICATION Semiconductor, DC
Common bus, DC drives,
Power converters/rectifiers

FUSE TYPE FWP-A14F

BREAKING CAPACITY AT NOMINAL VOLTAGE, AC 200 kA

BREAKING CAPACITY AT NOMINAL VOLTAGE, DC 50 kA

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-cylindrical-fuse-declaration-of-conformity-uk250904en.pdf](#)

□□□□□

[720025 FWP](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

