

## Eaton FWP-20A14FI

Eaton Bussmann series FWP high speed fuse, 690 Vac (IEC), 700 Vac (UL), 600 Vdc (UL), 20A, 200 kAIC at 700 Vac, 50 kAIC at 600 Vdc, With Indicator, High speed fuse, Ferrule end X ferrule end, Class aR, White, Ceramic

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWP-20A14FI
UPC	051712541015
PRODUCT LENGTH/DEPTH	52 mm
PRODUCT HEIGHT	15 mm
PRODUCT WIDTH	15 mm
PRODUCT WEIGHT	20.4 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	CSA Certified UL Recognized

<b>USED WITH</b>	Finger safe holders/blocks and striker
<b>AMPERAGE RATING</b>	20 A
<b>BREAKING CAPACITY</b>	200 kA
<b>FREQUENCY RATING - MAX</b>	62 Hz
<b>FREQUENCY RATING - MIN</b>	45 Hz
<b>FUSE INDICATOR</b>	Top fuse status indicator
<b>RELEASE CHARACTERISTIC</b>	Other
<b>UTILIZATION CATEGORY</b>	aR (accompanied semiconductor protection)
<b>VOLTAGE TYPE</b>	AC/DC
<b>FUSE SIZE</b>	14 x 51 mm
<b>RATED VOLTAGE AC</b>	700 V
<b>RATED VOLTAGE DC</b>	800 V
<b>CLASS</b>	Class aR
<b>CLEARING (I2T)</b>	180
<b>WATT LOSSES</b>	6.5 W
<b>FUSE SHAPE</b>	Cylindrical
<b>PRE ARC (I2T)</b>	26
<b>COLOR</b>	White
<b>INTERRUPT RATING</b>	200 kAIC
<b>FITTED WITH:</b>	Striker
<b>CONNECTION</b>	Ferrule end x ferrule end
<b>CONSTRUCTION SIZE</b>	14 mm x 51 mm
<b>MATERIAL</b>	Ceramic
<b>PACKAGING TYPE</b>	Standard
<b>QUANTITY</b>	10
<b>VOLTAGE RATING</b>	700 V
<b>TYPE</b>	High speed fuse
<b>APPLICATION</b>	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
<b>FUSE TYPE</b>	FWP-A14FI
<b>BREAKING CAPACITY AT NOMINAL VOLTAGE, AC</b>	200 kA
<b>BREAKING CAPACITY AT NOMINAL VOLTAGE, DC</b>	50 kA

[720025 FWP](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

