

## Eaton FWP-25G22FI

Eaton Bussmann series FWP high speed fuse, 690V, 25A, 200 kAIC, None, High speed fuse, Ferrule end X ferrule end

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed cylindrical fuse
<b>CATALOG NUMBER</b>	FWP-25G22FI
<b>UPC</b>	051712691772
<b>PRODUCT LENGTH/DEPTH</b>	58 mm
<b>PRODUCT HEIGHT</b>	22 mm
<b>PRODUCT WIDTH</b>	22 mm
<b>PRODUCT WEIGHT</b>	52.6 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	UL Recognized IEC Rated

<b>AMPERAGE RATING</b>	25 A
<b>ACCESSORIES</b>	CH22 Modular fuse holder
<b>BREAKING CAPACITY</b>	200 kA
<b>FREQUENCY RATING - MAX</b>	62 Hz
<b>FREQUENCY RATING - MIN</b>	45 Hz
<b>FUSE INDICATOR</b>	Top fuse status indicator
<b>RELEASE CHARACTERISTIC</b>	Other
<b>UTILIZATION CATEGORY</b>	gR (general purpose semiconductor protection)
<b>VOLTAGE TYPE</b>	AC
<b>FUSE SIZE</b>	22 x 58 mm
<b>RATED VOLTAGE AC</b>	690 V
<b>CLASS</b>	Class gR
<b>CLEARING (I2T)</b>	274
<b>WATT LOSSES</b>	6.65 W
<b>PRE ARC (I2T)</b>	43
<b>INTERRUPT RATING</b>	200 kAIC
<b>CONNECTION</b>	Ferrule end x ferrule end
<b>CONSTRUCTION SIZE</b>	Other
<b>MATERIAL</b>	Ceramic
<b>PACKAGING TYPE</b>	Standard
<b>VOLTAGE RATING</b>	690 V
<b>TYPE</b>	High speed fuse
<b>APPLICATION</b>	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
<b>FUSE TYPE</b>	FWP-G22FI
<b>BREAKING CAPACITY AT NOMINAL VOLTAGE, AC</b>	200 kA
<b>BREAKING CAPACITY AT NOMINAL VOLTAGE, DC</b>	50 kA

## DECLARATIONS OF CONFORMITY

[eaton-high-speed-cylindrical-fuse-declaration-of-conformity-uk250950en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

