

Eaton FWP-30A14F

Eaton Bussmann series FWP high speed fuse, 700 Vac (UL), 700 Vdc (UL), 690 Vac (IEC), 30A, 200 kAIC at 700 Vac, 50 kAIC at 700 Vdc, Non Indicating, High speed fuse, Ferrule end X ferrule end, Class aR, White, Ceramic

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWP-30A14F
UPC	051712795968
PRODUCT LENGTH/DEPTH	51 mm
PRODUCT HEIGHT	15 mm
PRODUCT WIDTH	15 mm
PRODUCT WEIGHT	20.3 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized CSA Certified

USED WITH	Finger safe holders/blocks and striker
AMPERAGE RATING	30 A
ACCESSORIES	• CH14 Modular fuse holder • FW14-PCB
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Non Indicating
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	14 x 51 mm
RATED VOLTAGE AC	700 V
RATED VOLTAGE DC	800 V
CLASS	Class aR
CLEARING (I2T)	400
WATT LOSSES	9 W
FUSE SHAPE	Cylindrical
MINIMUM MELTING	58 I2t (A2 sec)
PRE ARC (I2T)	58
COLOR	White
INTERRUPT RATING	200 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	14 mm x 51 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
QUANTITY	10
VOLTAGE RATING	700 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWP-A14F
BREAKING CAPACITY AT	200 kA

[720025 FWP](#)

NOMINAL VOLTAGE, AC	
BREAKING CAPACITY AT NOMINAL VOLTAGE, DC	50 kA

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

