

Eaton FWP-3A14F

Eaton Bussmann series FWP high speed fuse, 700V (UL), 3A, 200 kAIC, Non Indicating, High speed fuse, Ferrule end X ferrule end, Class aR, White, Ceramic

| | |
|----------------------|---|
| | |
| PRODUCT NAME | Eaton Bussmann series high speed cylindrical fuse |
| CATALOG NUMBER | FWP-3A14F |
| UPC | 051712795111 |
| PRODUCT LENGTH/DEPTH | 51 mm |
| PRODUCT HEIGHT | 15 mm |
| PRODUCT WIDTH | 15 mm |
| PRODUCT WEIGHT | 20.5 g |
| COMPLIANCES | CE Marked RoHS Compliant |
| CERTIFICATIONS | UL Recognized CSA Certified |

| | |
|--|--|
| | |
| USED WITH | Finger safe holders/blocks and striker |
| AMPERAGE RATING | 3 A |
| ACCESSORIES | <ul style="list-style-type: none"> • CH14 Modular fuse holder • FW14-PCB |
| BREAKING CAPACITY | 200 kA |
| FREQUENCY RATING - MAX | 62 Hz |
| FREQUENCY RATING - MIN | 45 Hz |
| FUSE INDICATOR | Non Indicating |
| RELEASE CHARACTERISTIC | Other |
| UTILIZATION CATEGORY | aR (accompanied semiconductor protection) |
| VOLTAGE TYPE | AC/DC |
| FUSE SIZE | 14 x 51 mm |
| RATED VOLTAGE AC | 700 V |
| CLASS | Class aR |
| CLEARING (I2T) | 0.26 |
| WATT LOSSES | 2.8 W |
| FUSE SHAPE | Cylindrical |
| PRE ARC (I2T) | 0.11 |
| COLOR | White |
| INTERRUPT RATING | 200 kAIC |
| CONNECTION | Ferrule end x ferrule end |
| CONSTRUCTION SIZE | 14 mm x 51 mm |
| MATERIAL | Ceramic |
| PACKAGING TYPE | Standard |
| QUANTITY | 10 |
| VOLTAGE RATING | 700 V |
| TYPE | High speed fuse |
| APPLICATION | Semiconductor, DC Common bus, DC drives, Power converters/rectifiers |
| FUSE TYPE | FWP-A14F |
| BREAKING CAPACITY AT NOMINAL VOLTAGE, AC | 200 kA |
| BREAKING CAPACITY AT NOMINAL VOLTAGE, DC | 50 kA |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| : |



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

