

## Eaton FWS-15A20FI

Eaton Bussmann series high speed traction fuse, 15A, 50 kAIC, With Indicator, Fuse, Class gS

PRODUCT NAME	Eaton Bussmann series high speed traction fuse
CATALOG NUMBER	FWS-15A20FI
UPC	051712640329
PRODUCT LENGTH/DEPTH	127 mm
PRODUCT HEIGHT	20 mm
PRODUCT WIDTH	20 mm
PRODUCT WEIGHT	96.9 g
COMPLIANCES	CE Marked
CERTIFICATIONS	IEC Rated

<b>AMPERAGE RATING</b>	15 A
<b>BREAKING CAPACITY</b>	50 kA
<b>WITH STRIKER</b>	Yes
<b>VOLTAGE TYPE</b>	AC/DC
<b>UTILIZATION CATEGORY</b>	gL/gG (cable protection/equipment protection)
<b>RELEASE CHARACTERISTIC</b>	Other
<b>FUSE INDICATOR</b>	With Indicator
<b>FREQUENCY RATING - MIN</b>	45 Hz
<b>FREQUENCY RATING - MAX</b>	62 Hz
<b>FUSE SIZE</b>	20 x 127 mm
<b>CLASS</b>	Class gG
<b>CLEARING (I2T)</b>	209 at 750 Vdc
<b>WATT LOSSES</b>	5 W
<b>FUSE SHAPE</b>	Cylindrical
<b>PRE ARC (I2T)</b>	209
<b>MOUNTING DIMENSION</b>	Other
<b>CURRENT TYPE</b>	AC
<b>RATED VOLTAGE AC</b>	1400 V
<b>RATED VOLTAGE DC</b>	1000 V
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	50 kA at 1000 Vdc
<b>CONSTRUCTION SIZE</b>	Other
<b>MATERIAL</b>	Ceramic
<b>PACKAGING TYPE</b>	Standard
<b>VOLTAGE RATING</b>	1400 V
<b>FUSE TYPE</b>	FWS-A20F
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	traction
<b>SUITABLE FOR</b>	CH127 Fuse holder
<b>BREAKING CAPACITY AT NOMINAL VOLTAGE, AC</b>	50 kA

## DECLARATIONS OF CONFORMITY

[eaton-high-speed-traction-fuse-declaration-of-conformity-uk250940en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

