

Eaton FWX-3A14F

Eaton Bussmann series FWX high speed fuse, 600V, 3A, 200 kAIC Vac, 50 kAIC at 250 Vdc, Non Indicating, High speed fuse, Ferrule end X ferrule end

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWX-3A14F
UPC	051712795159
PRODUCT LENGTH/DEPTH	58 mm
PRODUCT HEIGHT	35 mm
PRODUCT WIDTH	89 mm
PRODUCT WEIGHT	21.8 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized

AMPERAGE RATING	30 A
ACCESSORIES	• CH14 Modular fuse holder • FW14-PCB
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Non Indicating
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	14 x 51 mm
RATED VOLTAGE AC	250 V
CLASS	Class aR
WATT LOSSES	2.8 W
FUSE SHAPE	Cylindrical
INTERRUPT RATING	200 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	14 mm x 51 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWX-A14F
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	200 kA



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

