



Eaton FXSOLWRD

Eaton Conventional VAD, Conventional, VAD, EN54 Systems, Wall Mounted, Red Plastic , Red Flash, Deep Base

□□□□

PRODUCT NAME	Eaton Conventional VAD
CATALOG NUMBER	FXSOLWRD
PRODUCT LENGTH/DEPTH	66 mm
PRODUCT HEIGHT	67 mm
PRODUCT WIDTH	93 mm
PRODUCT WEIGHT	0.1 kg
COMPLIANCES	EN



Powering Business Worldwide



NOMINAL VOLTAGE	24 V
VOLTAGE TYPE	DC
ELECTRICITY CONSUMPTION	0.025 A
POWER	0.6 W
LENS COLOR	Red
MATERIAL HOUSING	Plastic
COLOR HOUSING	Other
MOUNTING METHOD	Surface mounting
NUMBER OF MODES	4
STANDBY-TIME UP TO	0 hour
AMBIENT TEMPERATURE - MAX	70 °C
AMBIENT TEMPERATURE - MIN	-25 °C
LAMP TYPE	LED not exchangeable
DEGREE OF PROTECTION (IP)	IP65
ALARM CURRENT - MAX	25 mA
ALARM CURRENT - MIN	10 mA
CONSTRUCTION MATERIAL	ABS
HUMIDITY (NON CONDENSING) - MAX	95 %
HUMIDITY (NON CONDENSING) - MIN	0 %
OPERATING TEMPERATURE - MAX	70 °C
OPERATING TEMPERATURE - MIN	-25 °C
SYSTEM TYPOLOGY	Conventional (Non-addressable)
PRODUCT BRANDING	Eaton Cooper
INTEGRATED FUNCTION	Flashlight
EN CERTIFICATION STANDARDS	EN54 Pt23 (Visual Alarms)
CABLE ENTRY	Rear
MOUNTING POSITION	Wall surface (internal)
LIGHT COLOR	Red
SYSTEM WIRING	2.5 mm
DIMMABLE	No
FUNCTION ROTATING LIGHT	NO
FUNCTION PULSATING LIGHT	YES



