



## Eaton FXSYG1WR-WP

Eaton Conventional sounder VAD,  
Conventional, Alarms and Beacons, Sounder  
VAD, EN54 Systems, Wall Mounted, Red  
Plastic, Red Flash, Weatherproof

□□□□

<b>PRODUCT NAME</b>	Eaton Conventional sounder VAD
<b>CATALOG NUMBER</b>	FXSYG1WR-WP
<b>PRODUCT LENGTH/DEPTH</b>	100 mm
<b>PRODUCT HEIGHT</b>	151 mm
<b>PRODUCT WIDTH</b>	111 mm
<b>PRODUCT WEIGHT</b>	0.2 kg
<b>COMPLIANCES</b>	EN



*Powering Business Worldwide*



<b>COMPLIANCE AND STANDARDS</b>	Accordance With EN 54-23
<b>NOMINAL VOLTAGE - MAX</b>	24 V
<b>NOMINAL VOLTAGE - MIN</b>	18 V
<b>TYPE OF CURRENT</b>	DC
<b>ELECTRICITY CONSUMPTION</b>	0.051 A
<b>POWER</b>	1.224 W
<b>LENS COLOR</b>	White
<b>LAMP TYPE</b>	LED
<b>SOUND OUTPUT</b>	100 dB
<b>TYPE OF OPTICAL SIGNAL</b>	Flash light
<b>TYPE OF ACOUSTIC SIGNAL DEVICE</b>	Sound generator
<b>TYPE OF ACOUSTIC SIGNAL</b>	Programmable
<b>MOUNTING METHOD</b>	Surface mounting
<b>COLOR HOUSING</b>	Red
<b>FREQUENCY SOUND SIGNAL - MAX</b>	1.2 Kilo Hertz
<b>FREQUENCY SOUND SIGNAL - MIN</b>	0.5 Kilo Hertz
<b>ALARM CURRENT - MAX</b>	51 mA
<b>ALARM CURRENT - MIN</b>	9 mA
<b>CONSTRUCTION MATERIAL</b>	ABS
<b>EN CERTIFIED TONES</b>	6
<b>HUMIDITY (NON CONDENSING) - MAX</b>	95 %
<b>HUMIDITY (NON CONDENSING) - MIN</b>	0 %
<b>OPERATING TEMPERATURE - MAX</b>	70 °C
<b>OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>SYSTEM TYPOLOGY</b>	Conventional (Non-addressable)
<b>TONES</b>	32
<b>VOICE TONES</b>	No
<b>PRODUCT BRANDING</b>	Eaton Cooper
<b>DEGREE OF PROTECTION</b>	IP66
<b>SUITABLE FOR</b>	Wall Mounting
<b>CABLE ENTRY</b>	Rear

