

# Eaton

## GHG2640021L0002

Eaton Crouse-Hinds series GHG26 disconnect switch, 80A, Six-pole, With switch, 2 x 1-1/2" NPT entries, 30 HP/50 HP, Fiberglass-reinforced polyester, 1 NC contact configuration, #12 AWG auxiliary, #2 AWG terminals, 690 Vac/120 Vdc

|                      |                                                   |
|----------------------|---------------------------------------------------|
|                      |                                                   |
| PRODUCT NAME         | Eaton Crouse-Hinds series GHG26 disconnect switch |
| CATALOG NUMBER       | GHG2640021L0002                                   |
| PRODUCT LENGTH/DEPTH | 10.67 in                                          |
| PRODUCT HEIGHT       | 10.67 in                                          |
| PRODUCT WIDTH        | 11.61 in                                          |
| PRODUCT WEIGHT       | 19.8 lb                                           |

## Certifications and compliances

|                                        |                                                                                                           |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------|
| <b>AREA CLASSIFICATION</b>             | Hazardous/Classified Locations                                                                            |
| <b>STANDARDS TYPE</b>                  | NEC/CEC<br>IECEX/ATEX                                                                                     |
| <b>NEC HAZARDOUS RATING</b>            | Class I, Zone 1<br>Class I, Zone 2<br>Class II, Division 1<br>Class I, Division 2<br>Class II, Division 2 |
| <b>NEMA RATING</b>                     | 4X                                                                                                        |
| <b>INGRESS PROTECTION (IP) RATINGS</b> | IP66                                                                                                      |

## Product specifications

|                         |                                                                 |
|-------------------------|-----------------------------------------------------------------|
| <b>ENCLOSURE TYPE</b>   | With switch                                                     |
| <b>AMPERAGE RATING</b>  | 80A                                                             |
| <b>CONFIGURATION</b>    | Six-pole                                                        |
| <b>VOLTAGE RATING</b>   | 690 Vac/120 Vdc                                                 |
| <b>ENTRY SIZE</b>       | 2 x 1-1/2" NPT                                                  |
| <b>HORSEPOWER</b>       | 30 hp/50 hp                                                     |
| <b>MATERIAL</b>         | Fiberglass-reinforced polyester                                 |
| <b>SPECIAL FEATURES</b> | 1 NC contact configuration, #12 AWG auxiliary, #2 AWG terminals |

[Eaton Specification Sheet - GHG2640021L0002](#)

[GHG26 Disconnect Switches flyer](#)

[GHG26 Series Explosion Protected Disconnect Switches catalog page](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

