



□□□□□

Eaton

GHG5124406R3001

Eaton Crouse-Hinds series IEC 60309 hazardous area interlock receptacle, 32A, Three-wire, four-pole, Nylon, M32, 380-415 Vac

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series IEC 60309 hazardous area interlock receptacle
CATALOG NUMBER	GHG5124406R3001
PRODUCT LENGTH/DEPTH	4.7 in
PRODUCT HEIGHT	11.5 in
PRODUCT WIDTH	6.6 in
PRODUCT WEIGHT	5.11 lb

Certifications and compliances	
AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC IEC
NEC HAZARDOUS RATING	Class I, Zone 1 Class I, Division 2 Class I, Zone 2
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Links	
Documents	Eaton Specification Sheet - GHG5124406R3001
Links	IEC 60309 Hazardous Area Pin and Sleeve Devices catalog page

Product specifications	
AMPERAGE RATING	32A
TRADE SIZE	M32
CONFIGURATION	Three-wire, four-pole
VOLTAGE RATING	380-415 Vac
MATERIAL	Nylon
