



Eaton

GHG5124409R3001

Eaton Crouse-Hinds series IEC 60309 hazardous area interlock receptacle, 32A, Three-wire, four-pole, Nylon, M32, 220-240 Vac

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series IEC 60309 hazardous area interlock receptacle
CATALOG NUMBER	GHG5124409R3001
PRODUCT LENGTH/DEPTH	119.38 mm
PRODUCT HEIGHT	292.1 mm
PRODUCT WIDTH	167.64 mm
PRODUCT WEIGHT	2.4 kg

Certifications and compliances	
AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	IEC NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Zone 1 Class I, Zone 2
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Links	
Links	IEC 60309 Hazardous Area Pin and Sleeve Devices catalog page
Links	Russian Customs Union - CEAG IEC 60309 Hazardous Area Devices

Product specifications	
AMPERAGE RATING	32A
TRADE SIZE	M32
CONFIGURATION	Three-wire, four-pole
VOLTAGE RATING	220-240 Vac
MATERIAL	Nylon
