



□□□□□

Eaton

GHG9601955R0004

Eaton Crouse-Hinds series Ex-e cable gland, Non-armoured cable, Non-armoured gland, Polyamide 6, Increased safety, M25, Short thread

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Ex-e cable gland
CATALOG NUMBER	GHG9601955R0004
PRODUCT LENGTH/DEPTH	37.5 mm
PRODUCT HEIGHT	29 mm
PRODUCT WIDTH	29 mm
PRODUCT WEIGHT	0.02 kg

Certifications and compliances		Product specifications	
AREA CLASSIFICATION	Hazardous/Classified Locations	PROTECTION TYPE	Increased safety
STANDARDS TYPE	IECEx/ATEX	CABLE TYPE	Non-armored Non-armoured
INGRESS PROTECTION (IP) RATINGS	IP66 IP68	GLAND TYPE	Non-armoured
		TYPE	Short thread
		THREAD SIZE	M25
		THREAD TYPE	Metric
		MATERIAL	Polyamide 6

Links	
Documents	Eaton Specification Sheet - GHG9601955R0004
Resources	Crouse-Hinds series CEAG GHG Non-metallic EX Cable Glands catalog page for North American applications
	Enlargement Gland IECEx Certificate of Conformity
	CEAG GHG Non-metallic Ex Cable Glands EU Type Examination Certificate
	Enlargement Gland Sizes M20 to M63 ATEX Certification

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE: