



□□□□□

Eaton

GHG9601955R0005

Eaton Crouse-Hinds series Ex-e cable gland,
Non-armoured cable, Non-armoured gland,
Polyamide 6, Increased safety, M32, Short
thread

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Ex-e cable gland
CATALOG NUMBER	GHG9601955R0005
PRODUCT LENGTH/DEPTH	45.5 mm
PRODUCT HEIGHT	36 mm
PRODUCT WIDTH	36 mm
PRODUCT WEIGHT	0.03 kg

Certifications and compliances	
AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	IECEX/ATEX
INGRESS PROTECTION (IP) RATINGS	IP66 IP68

Product specifications	
PROTECTION TYPE	Increased safety
CABLE TYPE	Non-armored Non-armoured
GLAND TYPE	Non-armoured
TYPE	Short thread
THREAD SIZE	M32
THREAD TYPE	Metric
MATERIAL	Polyamide 6

Links	
Documents	Eaton Specification Sheet - GHG9601955R0005
Links	Crouse-Hinds series CEAG GHG Non-metallic EX Cable Glands catalog page for North American applications
Links	Enlargement Gland Sizes M20 to M63 ATEX Certification
Links	CEAG GHG Non-metallic Ex Cable Glands EU Type Examination Certificate
Links	Enlargement Gland IECEx Certificate of Conformity

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton

Follow us on social media to get the latest product and support information.

