

Eaton GSB25

Fuse-link, high speed, 25 A, AC 600 V, BS88,
9 x 75 mm, aR, BS

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	GSB25
UPC	051712683746
PRODUCT LENGTH/DEPTH	18.2 mm
PRODUCT HEIGHT	18.2 mm
PRODUCT WIDTH	80 mm
PRODUCT WEIGHT	33.4 g
COMPLIANCES	CE

AMPERAGE RATING	25 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
RATED SWITCHING CAPACITY	100 kA
RATED VOLTAGE AC	600 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	64 mm
MOUNTING DIMENSION	M6
CURRENT TYPE	AC
CLASS	Class aR
FUSE SHAPE	Offset bolted tags
COLOR	None
CONSTRUCTION SIZE	Other
VOLTAGE RATING	600 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	GSB
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: