



Eaton GSGB45

Fuse-link, high speed, 45 A, AC 660 V, DC 400 V, BS88, 17 x 80 mm, aR, BS, Ultra fast

□□□□

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	GSGB45
UPC	051712392303
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	18 mm
PRODUCT WIDTH	18 mm
PRODUCT WEIGHT	33.3 g
COMPLIANCES	CE Marked
CERTIFICATIONS	UL Recognized



Powering Business Worldwide

□□□□

□□

AMPERAGE RATING	45 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	100 kA
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	400 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	61.8 mm
MOUNTING DIMENSION	M6
CURRENT TYPE	AC/DC
CLASS	Class aR
WATT LOSSES	10.8 W
FUSE SHAPE	Offset bolted tags
COLOR	None
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	GSG
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

