

Eaton GUAB24

Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 2" cover opening diameter, Feraloy iron alloy, B shape, 3/4"

PRODUCT NAME	Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover
CATALOG NUMBER	GUAB24
UPC	782274461304
PRODUCT LENGTH/DEPTH	2.5 in
PRODUCT HEIGHT	3.38 in
PRODUCT WIDTH	2.5 in
PRODUCT WEIGHT	1.75 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
NEMA RATING	3 4 7 9

Product specifications

SHAPE	B
TRADE SIZE	3/4"
COVER OPENING DIAMETER	2"
MATERIAL	Feraloy iron alloy

[IF 1730 - GUA/EAB/EAL
Condulet Outlet Boxes](#)

[Eaton Specification Sheet -
GUAB24](#)

[Crouse-Hinds series GUA
Conduit Outlet Boxes
catalog page](#)

[Industrial Fittings Bend
Radius and Cubic Capacity
Chart](#)

[Condulet GUA and GUR
Explosionproof Conduit
Outlet Boxes UL
certification](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

