

Eaton GUAL26 DIN16

Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, L shape, DIN rail mounted, 6 terminal blocks, 3/4"

PRODUCT NAME	Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover
CATALOG NUMBER	GUAL26 DIN16
UPC	662276707894
PRODUCT LENGTH/DEPTH	4.38 in
PRODUCT HEIGHT	4.38 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	2.65 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
NEMA RATING	3 4 7 9

Product specifications

SHAPE	L
TRADE SIZE	3/4"
COVER OPENING DIAMETER	3"
MATERIAL	Feraloy iron alloy
SPECIAL FEATURES	DIN rail mounted, 6 terminal blocks

[IF 1730 - GUA/EAB/EAJ
Condulet Outlet Boxes](#)

[Eaton Specification Sheet -
GUAL26 DIN16](#)

[Crouse-Hinds series GUA
Conduit Outlet Boxes catalog
page](#)

[Industrial Fittings Bend
Radius and Cubic Capacity
Chart](#)

[Condulet GUA and GUR
Explosionproof Conduit Outlet
Boxes UL certification](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:

Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.