



□□□□□

Eaton GUAT26 DIN14

Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, T shape, DIN rail mounted, 4 terminal blocks, 3/4"

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover
CATALOG NUMBER	GUAT26 DIN14
UPC	662276091856
PRODUCT LENGTH/DEPTH	5.25 in
PRODUCT HEIGHT	4.38 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	1 lb

Certifications and compliances	
AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
NEMA RATING	3 4 7 9

Links	
Conduit Boxes	IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes
Conduit Boxes	Eaton Specification Sheet - GUAT26 DIN14
Conduit Boxes	Crouse-Hinds series GUA Conduit Outlet Boxes catalog page
Conduit Boxes	Industrial Fittings Bend Radius and Cubic Capacity Chart
Conduit Boxes	Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

Product specifications	
SHAPE	T
TRADE SIZE	3/4"
COVER OPENING DIAMETER	3"
MATERIAL	Feraloy iron alloy
SPECIAL FEATURES	DIN rail mounted, 4 terminal blocks