



□□□□□

Eaton HP3.170-0200

Eaton HP3 Pressure Filter, HP3.
170.6VG.HR.E.P.-.G.5.-.AOC.5,0.P., 6VG,
Glass fiber fleece (VG), Nitrile, 6000 psi (420
Bar), Non-bypass

□□□□

PRODUCT NAME	Eaton HP3 Pressure Filter
CATALOG NUMBER	HP3.170-0200
PRODUCT LENGTH/DEPTH	130 mm
PRODUCT HEIGHT	367.77 mm
PRODUCT WIDTH	115.02 mm
PRODUCT WEIGHT	11.8 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. ATEX Directive 2014/34/EU AD 2000



Powering Business Worldwide

0000	
CONNECTION TYPE	G 1" threaded
DESIGN	Single open end
FILTER TYPE	High pressure filter
MATERIAL	EN-GJS-400-18-LT
APPLICATION	High pressure filters
SPECIFICATION	Standard
FILTER FINENESS	6 VG
FILTER MEDIA TYPE	Glass fiber fleece (VG)
INDICATOR TYPE	Visual
SEALING MATERIAL	Nitrile
ELEMENT COLLAPSE RATING	2320 psi (160 Bar)
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Non-bypass
OPERATING PRESSURE - MAX	6000 psi (420 Bar)

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000 Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

