



□□□□□

Eaton HP3.170-0216

Eaton HP3 Pressure Filter,
HP3.170.10VG.30.E.P.-.G.5.-.S2.-, 10 VG,
Glass fiber fleece (VG), Nitrile, 6000 psi (420
Bar), Bypass set at 102 psi (7 Bar)

□□□□

PRODUCT NAME	Eaton HP3 Pressure Filter
CATALOG NUMBER	HP3.170-0216
PRODUCT LENGTH/DEPTH	130.51 mm
PRODUCT HEIGHT	318.77 mm
PRODUCT WIDTH	115.02 mm
PRODUCT WEIGHT	11.8 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. ATEX Directive 2014/34/EU AD 2000

0000	
CONNECTION TYPE	G 1" threaded
FILTER TYPE	High pressure filter
MATERIAL	Carbon steel EN-GJS-400-18-LT
APPLICATION	High pressure filters
SPECIFICATION	Standard
CODE STAMP	None
FILTER FINENESS	10 VG
FILTER MEDIA TYPE	Glass fiber fleece (VG)
FLUID GROUP (DGRL 2014/68/EU)	2
INDICATOR TYPE	None
SEALING MATERIAL	Nitrile
ELEMENT COLLAPSE RATING	435 psi (30 Bar)
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Bypass set at 102 psi (7 Bar)
OPERATING PRESSURE - MAX	6000 psi (420 Bar)

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00: