

Eaton HPAB42574HR

Eaton Crouse-Hinds series Pauluhn Summit HPA linear fluorescent light fixture,3/4", (2) NPT hubs,50/60 Hz,4 ft lamp,Acrylic lens,T5HO mini bi-pin,Aluminum,2-lamp,High reflectance reflector,Through feed,Bolted door,120-277 Vac,54W

PRODUCT NAME	Eaton Crouse-Hinds series Pauluhn Summit HPA linear fluorescent light fixture
CATALOG NUMBER	HPAB42574HR
UPC	662276625204
PRODUCT LENGTH/DEPTH	50.59 in
PRODUCT HEIGHT	6.59 in
PRODUCT WIDTH	15.92 in
PRODUCT WEIGHT	34 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
NEMA RATING	4
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LAMP TYPE	Fluorescent
TYPE	Bolted door
MATERIAL	Aluminum
LAMP LENGTH	4 ft
NUMBER OF LAMPS	2-lamp
LIGHT TYPE	T5HO mini bi-pin
VOLTAGE RATING	120-277 Vac
FREQUENCY RATING	50/60 Hz
STYLE	Through feed
ENTRY SIZE	3/4"
ENTRY TYPE	(2) NPT hubs
WATTAGE	54W
LENS MATERIAL	Acrylic
SPECIAL FEATURES	High reflectance reflector

[IF LBL1403 - Pauluhn Summit Linear Fluorescent](#)

[Eaton Specification Sheet - HPAB42574HR](#)

[Crouse-Hinds series Pauluhn Summit Hazardous Area Linear Fluorescent brochure](#)

[Crouse-Hinds series Pauluhn Summit Hazardous Area Linear Fluorescent catalog page](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

