

Eaton HPF30-0000

Eaton HPF Manifold Mounted High Pressure Filter, HPF30.10VG.30.E.P.-.F.2.P.-.AE.50.5,0.P.-.-.-, 10 VG, Glass fiber fleece (VG), Nitrile, 4568 psi (315 Bar), Non-bypass

PRODUCT NAME	Eaton HPF, HPFO Manifold Mounted High Pressure Filter
CATALOG NUMBER	HPF30-0000
PRODUCT LENGTH/DEPTH	93 mm
PRODUCT HEIGHT	278 mm
PRODUCT WIDTH	50 mm
PRODUCT WEIGHT	2.4 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. AD 2000 ATEX Directive 2014/34/EU

CONNECTION TYPE	3/8" Manifold Mounted
FILTER TYPE	High pressure filter
MATERIAL	Carbon steel
RETENTION RATING	10.0 μ m
APPLICATION	Flange or manifold mounted in pressure lines
SPECIFICATION	Standard
CODE STAMP	None
FILTER FINENESS	10 VG
FILTER MEDIA TYPE	Glass fiber fleece (VG)
FLUID GROUP (DGRL 2014/68/EU)	2
INDICATOR TYPE	Electrical/Visual
SEALING MATERIAL	Nitrile
ELEMENT COLLAPSE RATING	435 psi (30 Bar)
OPERATING TEMPERATURE - MAX	80 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Non-bypass
OPERATING PRESSURE - MAX	4568 psi (315 Bar)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

