



□□□□□

Eaton HPF90-0002

Eaton HPF Manifold Mounted High Pressure Filter, HPF90.25VG.HR.E.P.VA.F.4.-.-
.AE.50.5,0.P.VA.-, 25 VG, Glass fiber fleece (VG), Nitrile, 4568 psi (315 Bar), Non-bypass

□□□□

PRODUCT NAME	Eaton HPF, HPFO Manifold Mounted High Pressure Filter
CATALOG NUMBER	HPF90-0002
PRODUCT LENGTH/DEPTH	96 mm
PRODUCT HEIGHT	348 mm
PRODUCT WIDTH	85 mm
PRODUCT WEIGHT	5.98 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. AD 2000 ATEX Directive 2014/34/EU



Powering Business Worldwide

0000

CONNECTION TYPE	3/4" Manifold Mounted
FILTER TYPE	High pressure filter
MATERIAL	Carbon steel
RETENTION RATING	20.0 μ m
APPLICATION	Flange or manifold mounted in pressure lines
SPECIFICATION	VA - stainless steel
CODE STAMP	None
FILTER FINENESS	25 VG
FILTER MEDIA TYPE	Glass fiber fleece (VG)
FLUID GROUP (DGRL 2014/68/EU)	2
INDICATOR TYPE	Electrical/Visual
SEALING MATERIAL	Nitrile
ELEMENT COLLAPSE RATING	2320 psi (160 Bar)
OPERATING TEMPERATURE - MAX	80 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Non-bypass
OPERATING PRESSURE - MAX	4568 psi (315 Bar)

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

