



Eaton HSR

Eaton Wheelock Exceder horn strobe, xenon, wall, red, FIRE, clear lens, 90/95/99 cd, 12/24V, indoor

□□□□

PRODUCT NAME	Eaton Wheelock Exceder horn strobe
CATALOG NUMBER	HSR
PRODUCT LENGTH/DEPTH	2.2 in
PRODUCT HEIGHT	5.24 in
PRODUCT WIDTH	4.56 in
PRODUCT WEIGHT	0.546 lb
COMPLIANCES	UL

COMPLIANCE AND STANDARDS	UL
	CSFM
	ULC
	FM
TYPE OF HORN STROBE	Horn strobe
HOUSING COLOR	Red
HOUSING MATERIAL	Plastic
LENS COLOR	Clear
LENS MATERIAL	Lexan
LAMP TYPE	Xenon
CURRENT DRAW (DC)	0.082/0.095/0.102/0.148/0.176/ 0.197/0.242/ 0.282
LETTERING	FIRE
OPERATING TEMPERATURE	32°F to 120°F (0°C to 49°C)
INDOOR/OUTDOOR	Indoor
MOUNTING METHOD	Wall
CANDELA SETTINGS	15 cd
	1575 cd
	30 cd
	75 cd
	95 cd
	110 cd
	135 cd
	185 cd
VOLTAGE	24 V
	12 V
TONES	Continuous Horn or Temporal (Code 3)
SOUND LEVEL (DBA)	95
	90
	99

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□: