



Eaton HSRC

Eaton Wheelock Exceder horn strobe,
xenon, ceiling, red, FIRE, clear lens, 90/95/99
cd, 12/24V, indoor

PRODUCT NAME	Eaton Wheelock Exceder horn strobe
CATALOG NUMBER	HSRC
UPC	786697274596
PRODUCT LENGTH/DEPTH	2.65 in
PRODUCT HEIGHT	6.64 in
PRODUCT WIDTH	6.64 in
PRODUCT WEIGHT	0.638 lb
COMPLIANCES	UL



COMPLIANCE AND STANDARDS	UL ULC CSFM FM
TYPE OF HORN STROBE	Horn strobe
HOUSING COLOR	Red
HOUSING MATERIAL	Plastic
LENS COLOR	Clear
LENS MATERIAL	Lexan
LAMP TYPE	Xenon
CURRENT DRAW (DC)	0.082/ 0.102/0.141/0.148/0.176/0.197/0.242/ 0.282
LETTERING	FIRE
OPERATING TEMPERATURE	32°F to 120°F (0°C to 49°C)
INDOOR/OUTDOOR	Indoor
MOUNTING METHOD	Ceiling
CANDELA SETTINGS	15 cd 30 cd 60 cd 75 cd 95 cd 115 cd 150 cd 177 cd
VOLTAGE	12 V 24 V
TONES	Continuous Horn or Temporal (Code 3)
SOUND LEVEL (DBA)	99 90 95



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

