



□□□□

Eaton I-ON1000EXKP

10 bus control panel, supplied with no zones, expands up to 1000 zones, European language version, Grade 2 or Grade 3, includes a Keypad with built in prox reader

□□□□

PRODUCT NAME	Eaton i-on1000EX intruder alarm panel
CATALOG NUMBER	I-ON1000EXKP
PRODUCT LENGTH/DEPTH	85 mm
PRODUCT HEIGHT	427 mm
PRODUCT WIDTH	420 mm
PRODUCT WEIGHT	6.65 kg
CERTIFICATIONS	CE marking



Powering Business Worldwide

BACK-UP BATTERY SIZE - MAX	17Ah
BACK-UP BATTERY QUANTITY	2
CLOUD SUPPORT	No
COMMUNICATIONS OPTIONS	On Board Ethernet. Plug on GSM, PSTN with two comm ports
CONNECTION	Hybrid
CUSTOM OUTPUTS	0
EMERGENCY POWER SUPPLY INTEGRATED	Yes
EN 50131 SECURITY GRADE	2 or 3
INTEGRATED DIAL DEVICE	Yes
LOG EVENTS	6500
NUMBER OF BUS DEVICES	250
NUMBER OF KEYPADS	250
NUMBER OF SABOTAGE GROUPS	1
NUMBER OF OUTPUTS FOR OPTICAL SIGNAL GENERATORS	2
OCCURRENCE MEMORY	Yes
ON BOARD OUTPUTS (PANEL)	8
ON BOARD OUTPUTS (PLUG BY)	16
OPERATING VOLTAGE	230 V
OUT OF THE BOX RADIO ZONES	0
OUT OF THE BOX WIRED ZONES	0
POWER SUPPLY SIZE	3.0A
RADIO CONNECTION	No
RADIO EXTERNAL SOUNDERS	0
RADIO INTERNAL SOUNDERS	0
SHUNT GROUPS	0
SUITABLE FOR BUS CONNECTION	Yes
SUPPORTS ARD	Yes
TOTAL CAPACITY ZONES	1000
USERS	999

