



□□□□

## Eaton I-ON40H

40 zone wired and wireless zone control panel, expands up to 80 zones using wired and wireless expanders, Grade 2, Eaton secureconnect enabled, built in Ethernet

□□□□

<b>PRODUCT NAME</b>	Eaton i-on40H intruder alarm panel
<b>CATALOG NUMBER</b>	I-ON40H
<b>PRODUCT LENGTH/DEPTH</b>	80 mm
<b>PRODUCT HEIGHT</b>	370 mm
<b>PRODUCT WIDTH</b>	240 mm
<b>PRODUCT WEIGHT</b>	1.95 kg
<b>CERTIFICATIONS</b>	CE marking



Powering Business Worldwide

<b>BACK-UP BATTERY SIZE - MAX</b>	7Ah
<b>BACK-UP BATTERY QUANTITY</b>	1
<b>CLOUD SUPPORT</b>	Yes
<b>COMMUNICATIONS OPTIONS</b>	On Board Ethernet. Plug on GSM, PSTN
<b>CONNECTION</b>	Hybrid
<b>CUSTOM OUTPUTS</b>	4
<b>EMERGENCY POWER SUPPLY INTEGRATED</b>	Yes
<b>EN 50131 SECURITY GRADE</b>	2
<b>INTEGRATED DIAL DEVICE</b>	No
<b>LOG EVENTS</b>	1000
<b>NUMBER OF BUS DEVICES</b>	20
<b>NUMBER OF KEYPADS</b>	20
<b>NUMBER OF SABOTAGE GROUPS</b>	41
<b>NUMBER OF OUTPUTS FOR OPTICAL SIGNAL GENERATORS</b>	2
<b>OCCURRENCE MEMORY</b>	Yes
<b>ON BOARD OUTPUTS (PANEL)</b>	3
<b>ON BOARD OUTPUTS (PLUG BY)</b>	12
<b>OPERATING VOLTAGE</b>	230 V
<b>OUT OF THE BOX RADIO ZONES</b>	30
<b>OUT OF THE BOX WIRED ZONES</b>	10
<b>POWER SUPPLY SIZE</b>	1A
<b>RADIO CONNECTION</b>	Yes
<b>RADIO EXTERNAL SOUNDERS</b>	4
<b>RADIO INTERNAL SOUNDERS</b>	4
<b>SHUNT GROUPS</b>	4
<b>SUITABLE FOR BUS CONNECTION</b>	Yes
<b>SUPPORTS ARD</b>	No
<b>TOTAL CAPACITY ZONES</b>	80
<b>USERS</b>	50
<b>VDS CLASS</b>	None

