



□□□□□

Eaton IHB24LP1/UNV1 SO10

Eaton Crouse-Hinds series IHB industrial high bay LED light, Cool, Non-dim driver, 400W-750W HID or 4-6-lamp T5HO, Glass lens, 24000 lm, 117 lm/W, Aluminum, Pend mt, Wide, 10 ft. SO cable, 3/4" trade size, 100-277 Vac, 127-250Vdc, 216W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series IHB industrial high bay LED light fixture
CATALOG NUMBER	IHB24LP1/UNV1 SO10
UPC	662276562721
PRODUCT LENGTH/DEPTH	18.83 in
PRODUCT HEIGHT	4.23 in
PRODUCT WIDTH	20.36 in
PRODUCT WEIGHT	27 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

LUMENS	24000
LUMENS PER WATT	117
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Pendant
TRADE SIZE	100-240 Vac, 127-250 Vdc
OPTICAL DISTRIBUTION	Wide
DIMMING	Non-dimmable driver
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
MATERIAL	Aluminum
LENS MATERIAL	Glass
WATTAGE	216W
EQUIVALENT LUMINAIRE	400W-750W HID or 4-6-lamp T5HO
POWER FACTOR	0.99
SPECIAL FEATURES	10 ft. SO cable

00000 [IF 1726 - Industrial High Bay LED Light Fixture](#)

00000000 [Eaton Specification Sheet - IHB24LP1/UNV1 SO10](#)

[Crouse-Hinds series industrial LED lighting solutions](#)

0000 [Crouse-Hinds series Industrial High Bay LED brochure](#)

[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds series DLC approved lighting products](#)

0000 [Crouse-Hinds series Industrial High Bay LED catalog page](#)

[Industrial High Bay LED Light Fixtures Canadian certification \(Luminaire Fittings\)](#)

0000 [Champ Pro PFM LED, Pauluhn Apex Industrial LED, Industrial High Bay LED and Weatherproof LED Light Fixtures Canadian certification](#)

[Industrial High Bay LED Light Fixtures UL certification \(Luminaire Fittings\)](#)

[Champ Pro PFM LED, Pauluhn Apex Industrial LED, Industrial High Bay LED and Weatherproof LED Light Fixtures UL certification](#)

