

Eaton JBXEA0G07MPSDS

Double nut receptacle, IP40, size 0, 7 male contacts; JBXEA0G07MPSDS

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXEA0G07MPSDS
PRODUCT LENGTH/DEPTH	18.2 mm
PRODUCT HEIGHT	12 mm
PRODUCT WIDTH	12 mm
PRODUCT WEIGHT	5.24 g
COMPLIANCES	UL 1977

CURRENT RATING	2.5 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	RoHS REACH
TEST CURRENT	2.5 A UL
TEST VOLTAGE	320 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT TYPE	PCB
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP40
LAYOUT	7
PLATING	Nickel Chrome
SHELL MATERIAL	Brass
SHELL SIZE	0
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Double Nut (Rear & Front)
NUMBER OF CONTACTS	7
NUT MATERIAL	Aluminium
SALT SPRAY	48 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

