



□□□□□

Eaton JBXEC2G16FPSDS

Double nut receptacle, IP68, size 2, 16 female contacts; JBXEC2G16FPSDS

□□□□

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXEC2G16FPSDS
PRODUCT LENGTH/DEPTH	26.5 mm
PRODUCT HEIGHT	20 mm
PRODUCT WIDTH	20 mm
PRODUCT WEIGHT	20.41 g
COMPLIANCES	UL 1977

□□□□	
CURRENT RATING	6 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	REACH RoHS
TEST CURRENT	6 A UL
TEST VOLTAGE	730 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	PCB
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP68
LAYOUT	16
PLATING	Nickel Chrome
SHELL MATERIAL	Brass
SHELL SIZE	2
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Double Nut (Rear & Front)
NUMBER OF CONTACTS	16
NUT MATERIAL	Aluminium
SALT SPRAY	48 hour

□□

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□: