

Eaton

JBXER1G10MSSDSR

Front mount receptacle, IP40, size 1, 10 male contacts; JBXER1G10MSSDSR

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXER1G10MSSDSR
PRODUCT LENGTH/DEPTH	18.7 mm
PRODUCT HEIGHT	14 mm
PRODUCT WIDTH	14 mm
PRODUCT WEIGHT	8.74 g
COMPLIANCES	UL 1977

CURRENT RATING	2.5 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	RoHS REACH
TEST CURRENT	2.5 A UL
TEST VOLTAGE	300 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Solder Cup
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP40
LAYOUT	10
PLATING	Nickel Chrome
SHELL MATERIAL	Brass
SHELL SIZE	1
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Front Mount Panel
NUMBER OF CONTACTS	10
NUT MATERIAL	Aluminium
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: