

Eaton

JBXER2G19MCNDSR

Front mount receptacle, IP40, size 2, 19 male contacts; JBXER2G19MCNDSR

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXER2G19MCNDSR
PRODUCT LENGTH/DEPTH	20.4 mm
PRODUCT HEIGHT	18 mm
PRODUCT WIDTH	18 mm
PRODUCT WEIGHT	15.55 g
COMPLIANCES	UL 1977

CURRENT RATING	5 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	RoHS REACH
TEST CURRENT	5 A UL
TEST VOLTAGE	660 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP40
LAYOUT	19
PLATING	Black Anodized
SHELL MATERIAL	Brass
SHELL SIZE	2
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Front Mount Panel
NUMBER OF CONTACTS	19
NUT MATERIAL	Aluminium
SALT SPRAY	96 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: