

Eaton

JBXER3G03MCNDSR

Front mount receptacle, IP40, size3, 3 male contacts; JBXER3G03MCNDSR

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXER3G03MCNDSR
PRODUCT LENGTH/DEPTH	24.5 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	22 mm
PRODUCT WEIGHT	23.45 g
COMPLIANCES	UL 1977

CURRENT RATING	25 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	REACH RoHS
TEST CURRENT	25 A UL
TEST VOLTAGE	1600 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP40
LAYOUT	3
PLATING	Black Anodized
SHELL MATERIAL	Brass
SHELL SIZE	3
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Front Mount Panel
NUMBER OF CONTACTS	3
NUT MATERIAL	Aluminium
SALT SPRAY	96 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

