

Eaton JBXER3G14FSNDSR

Front mount receptacle, IP40, size 3, 14 female contacts; JBXER3G14FSNDSR

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXER3G14FSNDSR
PRODUCT LENGTH/DEPTH	24.5 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	22 mm
PRODUCT WEIGHT	25.72 g
COMPLIANCES	UL 1977

CURRENT RATING	9 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	RoHS REACH
TEST CURRENT	9 A UL
TEST VOLTAGE	830 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Solder Cup
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP40
LAYOUT	14
PLATING	Black Anodized
SHELL MATERIAL	Brass
SHELL SIZE	3
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Front Mount Panel
NUMBER OF CONTACTS	14
NUT MATERIAL	Aluminium
SALT SPRAY	96 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: