

Eaton

JBXER3G18MSNDSR

Front mount receptacle, IP40, size3, 18 male contacts; JBXER3G18MSNDSR

| | |
|---------------------------------|--|
| PRODUCT NAME | Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector |
| CATALOG NUMBER | JBXER3G18MSNDSR |
| PRODUCT LENGTH/DEPTH | 24.5 mm |
| PRODUCT HEIGHT | 22 mm |
| PRODUCT WIDTH | 22 mm |
| PRODUCT WEIGHT | 25.74 g |
| COMPLIANCES | UL 1977 |



Powering Business Worldwide

| | |
|------------------------------------|--------------------------|
| CURRENT RATING | 7 A UL |
| FITTED WITH: | Shielding |
| ENVIRONMENTAL CONDITIONS | REACH RoHS |
| TEST CURRENT | 7 A UL |
| TEST VOLTAGE | 660 V UL |
| CONNECTOR ACCESSORY OPTION | No backshell possibility |
| CONNECTOR TYPE | Receptacle |
| CONTACT DELIVERY | Loaded |
| CONTACT GENDER | Pin (Male) |
| CONTACT TYPE | Solder Cup |
| COUPLING TYPE | Push-Pull |
| DEGREE OF PROTECTION | IP40 |
| LAYOUT | 18 |
| PLATING | Black Anodized |
| SHELL MATERIAL | Brass |
| SHELL SIZE | 3 |
| MATING CYCLES | 5000 |
| OPERATING TEMPERATURE - MAX | 125 °C |
| OPERATING TEMPERATURE - MIN | -40 °C |
| RECEPTACLE TYPE | Front Mount Panel |
| NUMBER OF CONTACTS | 18 |
| NUT MATERIAL | Aluminium |
| SALT SPRAY | 96 hour |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
 30 Pembroke Road
 Dublin 4,
 Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

