

## Eaton JBXEZ0G05FPNDSR

PCB rear mount receptacle with pins, IP40, size 0, 5 female contacts; JBXEZ0G05FPNDSR

|                                 |                                                                          |
|---------------------------------|--------------------------------------------------------------------------|
|                                 |                                                                          |
| <b>PRODUCT NAME</b>             | Eaton Souriau JBX series<br>IP40 / IP68 metallic push-<br>pull connector |
| <b>CATALOG NUMBER</b>           | JBXEZ0G05FPNDSR                                                          |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 23 mm                                                                    |
| <b>PRODUCT HEIGHT</b>           | 10 mm                                                                    |
| <b>PRODUCT WIDTH</b>            | 10 mm                                                                    |
| <b>PRODUCT WEIGHT</b>           | 8.89 g                                                                   |
| <b>COMPLIANCES</b>              | UL 1977                                                                  |

|                             |                          |
|-----------------------------|--------------------------|
|                             |                          |
| CURRENT RATING              | 6.5 A UL                 |
| FITTED WITH:                | Shielding                |
| ENVIRONMENTAL CONDITIONS    | REACH<br>RoHS            |
| TEST CURRENT                | 6.5 A UL                 |
| TEST VOLTAGE                | 400 V UL                 |
| CONNECTOR ACCESSORY OPTION  | No backshell possibility |
| CONNECTOR TYPE              | Receptacle               |
| CONTACT DELIVERY            | Loaded                   |
| CONTACT GENDER              | Socket (Female)          |
| CONTACT TYPE                | PCB                      |
| COUPLING TYPE               | Push-Pull                |
| DEGREE OF PROTECTION        | IP40                     |
| LAYOUT                      | 5                        |
| PLATING                     | Black Anodized           |
| SHELL MATERIAL              | Brass                    |
| SHELL SIZE                  | 0                        |
| MATING CYCLES               | 5000                     |
| OPERATING TEMPERATURE - MAX | 125 °C                   |
| OPERATING TEMPERATURE - MIN | -40 °C                   |
| RECEPTACLE TYPE             | Rear Mount Panel         |
| NUMBER OF CONTACTS          | 5                        |
| SALT SPRAY                  | 96 hour                  |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

