

Eaton

JBXEZ0G06MPSDSR

PCB rear mount receptacle with pins, IP40,
size 0, 6 male contacts; JBXEZ0G06MPSDSR

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXEZ0G06MPSDSR
PRODUCT LENGTH/DEPTH	23 mm
PRODUCT HEIGHT	10 mm
PRODUCT WIDTH	10 mm
PRODUCT WEIGHT	8.36 g
COMPLIANCES	UL 1977

CURRENT RATING	2.5 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	REACH RoHS
TEST CURRENT	2.5 A UL
TEST VOLTAGE	320 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT TYPE	PCB
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP40
LAYOUT	6
PLATING	Nickel Chrome
SHELL MATERIAL	Brass
SHELL SIZE	0
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Rear Mount Panel
NUMBER OF CONTACTS	6
SALT SPRAY	48 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

