

Eaton JBXEZ1G10FPNDSR

PCB rear mount receptacle with pins, IP40,
size 1, 10 female contacts;
JBXEZ1G10FPNDSR

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXEZ1G10FPNDSR
PRODUCT LENGTH/DEPTH	25 mm
PRODUCT HEIGHT	12 mm
PRODUCT WIDTH	12 mm
PRODUCT WEIGHT	12.83 g
COMPLIANCES	UL 1977

CURRENT RATING	2.5 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	REACH RoHS
TEST CURRENT	2.5 A UL
TEST VOLTAGE	300 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	PCB
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP40
LAYOUT	10
PLATING	Black Anodized
SHELL MATERIAL	Brass
SHELL SIZE	1
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Rear Mount Panel
NUMBER OF CONTACTS	10
SALT SPRAY	96 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

