

Eaton

JBXFC0G05FCNDSMR

Right angle plug, IP40, size 0, 5 female contacts, cable clamp protective boot; JBXFC0G05FCNDSMR

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXFC0G05FCNDSMR
PRODUCT LENGTH/DEPTH	30.5 mm
PRODUCT HEIGHT	29.5 mm
PRODUCT WIDTH	10 mm
PRODUCT WEIGHT	14.21 g
COMPLIANCES	UL 1977



CURRENT RATING	6.5 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	RoHS REACH
TEST CURRENT	6.5 A UL
TEST VOLTAGE	400 V UL
BACKSHELL ANGLE	90°
BACKSHELL TYPE	Sealing Gland With Optional Boot
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP40
LAYOUT	5
PLATING	Black Anodized
PLUG TYPE	Right Angle Plug
SHELL MATERIAL	Brass
SHELL SIZE	0
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	5
SALT SPRAY	96 hour



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

